


User Guide Addendum

NuRAD R2

Firmware v.1.6.6



Johan Berglund

2025-06-13

Overview

The NuRAD R2 (revision 2) has some difference in controls over the original NuRAD. The main keys are now have a slightly concave top to make it easier to feel finger position, and the rollers are a bit wider while still keeping the same thumb movement range. The right hand thumb lever has been replaced by a ground pad and a touch pad is placed in front of the thumb. This pad allows easier control of glide or CC while still being able to do vibrato. A glide strip has been added in front of the thumb by the rollers. This can be configured to control glide or CC. Glide has also been added as a destination for the extra controller (lip sensor). As for controller outputs, they are just like on the original NuRAD with the exception of the 3.5 mm TS jack on the side for 5V level breath CV, which has been removed (due to not getting much use out in the wild). The CV on the 5-pin DIN MIDI jack is still there, for use with Berglund CV modules like CVX and CVXG, or the standalone NuMar and "Gray Mini" analog synth boxes.

Changes in the menu

As the lever is now a pad, the menu items LVR CTL and LVR CC are now renamed PAD CTL and LVR CC. Likewise in the VIBRATO menu the SENSE LVR and SQUELCH L are now SENSE PAD and SQUELCH L. Naturally also in the adjust menu, the page is labeled PAD instead of LVR.

For the extra controller, the item GLD has been added as a destination. This links the control to the glide routines and menu items GLIDE MOD, GLIDE MAX and GLIDE MIN will further decide the corresponding glide CC outputs.

The new glide strip adds two new menu items in the SETUP CTR menu – STRIP CTL and STRIP CC. STRIP CTR can be set to OFF, GLD (default) or CC. STRIP CC sets the CC number to send when the strip control is set to CC.

Like with the PAD, the adjust menu label has been changed, and it is now GLS/EC. Now there are two sensor dots visible in the SNS row, one for the glide strip and one for the lip sensor. Like with the pitch bender, the threshold and max bars are valid for both sensor inputs.